

CHYUN JYE

自動充填機 AUTOMATIC LIQUID FILLING MACHINE



MODEL :
AF-80




ISO 9001 :2000



039

0 1 5 9 9 0



CHYUN JYE




群捷機械有限公司
CHYUN JYE MACHINERY CO., LTD.
公司：桃園縣龜山鄉龍壽村龍校街121巷2弄4號
E-mail:chyunjye@ms15.hinet.net
http://www.chyunjye.com

FACTORY : 1F, NO. 4, ALLEY 2, LANE 121, LUNG
HSIAO STREET, LUNG-SHOU VILLAGE KUEI SHAN
HSIANG, TAO YUAN HSIEN, TAIWAN, R.O.C.
TEL : 886-3-320-5757 FAX : 886-3-3295378

MODEL : AF-80

Specifications 詳細規格

Models	機 型	AF-80
Filling Capacity	充填容量	5cc-60cc 30cc-150cc 100cc-500cc
Speed	生產速度	30-50 pcs/min
Power Motor	馬達馬力	1/2 HP
Power Source	電源	220/380V 60/50 HZ
Machine Dimension	機器尺寸	2200Lx880Wx1490H (mm)
Machine Weight	機器重量	500 Kgs
Air Press	空氣壓力	3-6 Kgs
Vacuum Press Consumption	空氣消耗量	200 L/min



特性：

採用單軸調整活塞，能迅速精確的調整所需之容量，活塞及液體接觸部位，採用不銹鋼及經硬烙處理，加強表面硬度。

進瓶、定位、操作動作，採用空氣缸運動，有安全裝置，瓶身傾倒，定位不正確，使用手動輪時均會自動停止一切動作。有緩衝機構可減低機件磨損，增長使用時間，調整軌道，清洗簡單容易。採用無段變速馬達，操作速度可自由調整，可單獨作業，亦可銜接自動封蓋機及自動貼標籤機。

一貫作業生產線，自動控制，無瓶子不會充填，充填嘴下降後充填，作業符合G.M.P標準。

應用：

適用於藥品、飲料、醬油、洗潔精、洗髮精、化學藥品等液體之填充作業。

Characteristics :

A desired capacity can be quickly and precisely acquired as the machine adapt a single axis adjusting piston. The contact parts with liquid of pump are made of stainless steel and piston, cylinder are hard chrome plated to enforce the surface hardness. Bottle feeding, position are operated pneumatically, different bottles are workable by a simple adjustment. A safety device is attached to the machine to stop the running, automatically in case of any fell down of bottle or during the running by hand-wheel. Surface are made of stainless steel for easy clean. The buffering device permits the less friction of mechanism, so as to prolong the service life of machine. A stepless speed variable motor is used for freely speed adjustment. this machine can be run independently or connected to automatic.

capping machine, automatic labeling machine for a complete integrated automatic operation. Filling nozzles fall down into bottle to fill with feeding, positioning in line to meet with G.M.P standard.

Application :

Suitable for filling various liquids, such as: medicine, soft drink, soybean sauce, chemical, shampoo, cleaning solution etc.